

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 1 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

1.0 Objective

This specification defines the performance, test, quality and reliability requirements of the BarKlip I/O Cable system.

2.0 Scope

This specification is applicable to the termination characteristics of the BarKlip I/O Cable System which provides a means of bringing high current from Busbar to system.

3.0 Ratings

- 3.1 Operating Voltage Rating = 480 VDC (The voltage rating is also dependant on the application)
- 3.2 Operating Current Rating = 200 A
- 3.3 Operating Temperature Range = -40 °C to +105 °C

4.0 Applicable Documents

- 4.1 FCI Specifications
 - 4.1.1 Engineering drawing 10129052 / 10129172/10134195
- 4.2 Industry or Trade Association standards
 - 4.2.1 Telcordia GR-1217
- 4.3 National or International Standards
 - 4.3.1 Flammability: UL-94V-0
 - 4.3.2 EIA 364: Electrical Connector/Socket Test Procedures Including Environmental Classifications
- 4.4 Safety Agency Approvals
 - 4.4.1 CSA std. C22.2 No. 182.3-M1987
 - 4.4.2 UL-1977

5.0 Requirements

- 5.1 Qualification

Connectors furnished under this specification shall be capable of meeting the qualification test requirements specified herein.
- 5.2 Material

The material for each component shall be as specified herein or equivalent.

 - Power Contacts – High Conductivity Copper alloy
 - Clip – Stainless steel
 - Housing – Thermoplastic, UL 94V-0

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 2 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

5.3 Finish

The finish for applicable components shall be as specified herein or equivalent.

Contact area: Silver over Nickel

5.4 Design and Construction

Connectors shall be of the design, construction, and physical dimensions specified on the applicable product drawing. There shall be no cracks, burrs, or other physical defects that may impair performance.

5.5 Connectors Mating Part (Busbar)

Recommended material: Copper, solid blade


Material Thickness: 3.0 ± 0.1 mm

Smallest nominal pitch at contacting area: 17 mm

Surface roughness in contact area: Ra 1.6 μ m maximum

Plating in contact area: 3 μ m min Silver over 1.27 μ m min Nickel

The Bus Bar dimensions as shown in below:



6.0 Electrical Characteristics

6.1 Contact Resistance, Low Level (LLCR)

6.1.1 The low level contact resistance shall not exceed 0.2 milliohms with silver plated Busbar initially and after any treatment and/or environmental exposure. Measurements shall be in accordance with EIA 364-23

The following details shall apply:

- Test Voltage - 20 mV DC Max. open circuit.
- Test Current - 100 mA DC Max.

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 3 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

6.1.2 Power contacts tested at specified Current (150A DC):

- a. The contact resistance at a specified current shall not exceed 0.2 mΩ (milliohms) with silver plated Busbar initially and after test only applicable to group 7 when measured in accordance with EIA 364-06.

6.2 Insulation Resistance

The insulation resistance of mated connectors shall not be less than 5000 Megohms initially and 1000 Megohms after environmental exposure.

Measurements shall be in accordance with EIA 364-21.

The following details shall apply:

- a. Test Voltage - 500 volts DC.
- b. Electrification Time - 1 minute

6.3 Dielectric Withstanding Voltage

There shall be no evidence of arc-over, insulation breakdown when mated connectors are tested in accordance with EIA 364-20.

The following details shall apply:

- a. Test Voltage - 1000 Volts RMS, AC.
- b. Test Duration - 60 seconds.

6.4 Current Rating

6.4.1 The temperature rise above ambient shall not exceed 30 °C at any point in the connector system when all contacts are powered at 200A with Silver plated Busbar.

- a. Reference - EIA 364-70

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 4 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

7.0 Mechanical Characteristics

7.1 Mating/Un-mating Force

	Mating force	Un-mating force
Single port (10129172)	40.0N Max	6.0N Min
Dual port (10129052/10134195)	80.0N Max	12.0N Min

The following details shall apply:

- a. Cross Head Speed: 25.4 mm per minute.
- b. Utilize free floating fixtures.
- c. The bus bar thickness is 3.00+/-0.10mm
- d. EIA 364-13, Method A
- e. The pitch of the Bus bar conductor in the test-tool is 17.0mm for dual port connector.

7.2 Durability (preconditioning) - EIA 364-09

The connector pairs shall be capable of withstanding 50 mating/un-mating cycles. When used for pre-conditioning treatment, 20 mating/un-mating cycles shall be applied prior to mechanical/environmental exposure.

- a. Cycling Rate: 127 mm per minute maximum
- b. Use free floating fixtures

7.3 Durability - EIA 364-09

With connector mate and un-mate samples for 50 cycles with a bus bar conductor.

- a. Cycling Rate: 127 mm per minute.
- b. Use free floating fixtures

7.4 Mechanical Shock –EIA 364-27

- a. Condition - A (50G, 11 millisecond, half-sine pulses type)
- b. Shocks - 3 shocks in both directions along each of three orthogonal axes (18 shocks total)
- c. Mounting - Rigidly mount assemblies
- d. No discontinuities greater than 1.0 microsecond

7.5 Random Vibration – EIA 364-28

- a. Test Condition - Test Condition V, Test condition C (50-2000Hz, 9.26g rms)
- b. Duration – 120 minutes along each of three orthogonal axes

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 5 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

- c. Mounting - Rigidly mount assemblies
- d. No discontinuities greater than 1.0 microseconds

7.6 Welding contact tensile strength

- a. EIA 364-13, Method A
- b. Tensile strength: 390N Minimum for 1x8 AWG; 550N Minimum for 2x8 AWG

7.7 Reseating

- Manually un-mate/mate the interconnect system once.
- a. Sample Size – Dependent upon current test group, refer to specific sample sizes.
- b. Failure Criteria - No evidence of physical damage.
- c. No lubrication to be used during cycling.

8.0 Environmental Conditions

After exposure to the following environmental conditions in accordance with the specified test procedure and/or details, the product shall show no physical damage and shall meet the electrical and mechanical requirements per paragraphs 6.0 and 7.0 as specified in the Table 1 test sequences. Unless specified otherwise, assemblies shall be mated during exposure.

8.1 Thermal Shock –EIA 364-32

- a. Number of Cycles –Method A, Test condition II, 25 cycles.
- b. Temperature Range – Between -65 °C and +105 °C
- c. Time at Each Temperature - 30 minutes minimum
- d. Transfer Time - 5 minutes, maximum

8.2 Cycling Temperature & Humidity –EIA 364-31, method III, condition B

- a. Relative Humidity and temperature - between 25°C and 65°C at 80% to 98% relative humidity
- b. Duration – 10 days
- c. Omitting 7b vibration test

8.3 High Temperature Life –EIA 364-17, Method A.

- a. Test Temperature - 105 °C
- b. Test Duration - 1000 hours
- c. Pre-condition - Perform 20 cycles of durability for product

8.4 Mixed Flowing Gas corrosion (MFG) –EIA 364-65

- a. Class - IIA
- b. Duration - 14 days
- c. ½ of samples mated for 336 hours, ½ of samples unmated for 168 hours, then mated for final 168 hours.
- d. After 7 days duration, test the LLCR. After 14 days duration, also test the LLCR.

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 6 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

8.5 Thermal disturbance-EIA 364-110

- a. The test specimens shall be mated during the test.
- b. Temperature Range – +15°C±3°C to +85°C±3°C
- c. Thermal Ramp – minimum of 2°C per minute.
- d. Dwell time to ensuring that the contacts reach the temperature extremes for a minimum of 5 minutes.
- e. Number of cycles – 10.
- f. Humidity does not need to be controlled during this portion of the test.

8.6 High Temperature Life(preconditioning) –EIA 364-17, Method A.

- a. Test Temperature - 105 °C
- b. Test Duration - 72 hours

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
TITLE BarKlip I/O Cable Connector		PAGE 7 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

9.0 Quality assurance provisions

9.1 Equipment Calibration

All test equipment and inspection facilities used in the performance of any test shall be maintained in a calibration system in accordance with ISO 9000.

9.2 Inspection Conditions

Unless otherwise specified herein, all inspections shall be performed under the following ambient conditions:

- a. Temperature : 25 +/- 5 °C
- b. Relative Humidity: 30% to 60%
- c. Barometric Pressure: Local ambient

9.3 Sample Quantity and Description

The sample size and description for each test is listed in table 1

9.4 Acceptance

9.4.1 Electrical and mechanical requirements placed on test samples as indicated in paragraphs 6.0 and 7.0 shall be established from test data using appropriate statistical techniques or shall otherwise be customer specified, and all samples tested in accordance with this product specification shall meet the stated requirements.

9.4.2 Failures attributed to equipment, test setup, or operator error shall not disqualify the product. If product failure occurs, corrective action shall be taken and samples resubmitted for qualification.

9.5 Qualification Testing

Qualification testing shall be performed on sample units produced with equipment and procedures normally used in production. The test sequences shall be as shown in the qualification test table 1.

9.6 Re-Qualification Testing

If any of the following conditions occur, the responsible product engineer shall initiate requalification testing consisting of all applicable parts of the qualification test matrix.

- a. A significant design change is made to the existing product which impacts the product form, fit or function. Examples of significant changes shall include, but not be limited to, changes in the plating material composition or thickness, contact force, contact surface geometry, insulator design, contact base material, or contact lubrication requirements.
- b. A significant change is made to the manufacturing process which impacts the product form, fit or function.
- c. A significant event occurs during production or end use requiring corrective action to be taken relative to the product design or manufacturing process.

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION		
TITLE BarKlip I/O Cable Connector			
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
CLASSIFICATION UNRESTRICTED			


9.7 Qualification Test Table 1

Test Sequence Table 1


Test Items	Section	Test Group									
		1	2	3	4	5	6	7	8	9	10
		Test Sequence									
Examination of Product	5.4	1,8	1,8	1,10	1,10	1,11	1,7	1,4	1,3		
Contact Resistance (Low Level)	6.1	2,7	2,5,7	2,5,7,9	2,5,7,9	2,5,7 (After7days), 8 (After14days), 10		3			
Insulation Resistance	6.2						2,5				
Dielectric Withstanding Voltage	6.3						3,6				
Current Rating (T-rise: 30°C Max.)	6.4							2			
Mating force	7.1	3,									
Un-mating Force	7.1	4,6									
Durability (Preconditioning)	7.2		3	3	3	3					
Durability	7.3	5					4				
Mechanical Shock	7.4				6						
Random Vibration	7.5				8						
welding contact tensile strength	7.6								2		
Reseating	7.7		6	8		9					
Thermal Shock	8.1			4							
Cycling Temperature and Humidity	8.2			6							
High Temperature Life	8.3		4								
Mixed Flowing Gas	8.4					6					
Thermal disturbance	8.5										
High Temperature Life (preconditioning)	8.6				4	4					
Samples quantity(PCS)		5	5	5	5	5	5	3	5		

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
TITLE BarKlip I/O Cable Connector		PAGE 9 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

10.1 Current temperature de-rating curve:



10.2 Temperature rise vs current curve:



Above rating is for reference only. Appropriate de-rating is required per ambient conditions, bus bar size to achieve thermal balance, gross heating from adjacent components, and other factors that influence connector performance.

NUMBER GS-12-1222	TYPE PRODUCT SPECIFICATION	Amphenol FCI	
BarKlip I/O Cable Connector		PAGE 10 of 10	REVISION 7
		AUTHORIZED BY Terris Liu	DATE 20 Feb 16
		CLASSIFICATION UNRESTRICTED	

REVISION RECORD

<u>Rev</u>	<u>Page</u>	<u>Description</u>	<u>EC#</u>	<u>Date</u>
7	All	Preliminary released	TBD	2016-02-20