



SIX.025.045.100.B.C.B

Biosensor transmitter

For bioanalytical applications


A product of Jobst Technologies

Benefits & Characteristics

- 6-channel poly-potentiostat with fixed working potential
- Evaluation Kit compatible with B.LV5 and B.IV4 enzymatic biosensors
- Bipolar current measurement range
- Evaluation software Biomon available for Windows
- Easy connectivity with USB or TTL UART
- For industrial applications

Illustration

„Six“ with TTL UART-connectivity for OEM integration (dimensions in mm):



Technical Data


Dimensions (L x W x H in mm):	75 x 38 x 7
Digital interface (serial protocol syntax supplied):	Bare TTL UART (3.3V)
Power:	+3.3 V to +5V supply required; 5 mA
Compliance:	±1 V
Current (min/max):	-50 nA to +50 nA (per channel)
Current resolution:	2 pA (typical RMS noise: 20 pA)
Working voltage:	+0.45 V (working vs. reference electrode)
Readings per second:	0.6
Temperature compensation:	Built-in on board
Connector type:	Right angle micro edge card socket (MEC6-RA, 40, 0.635 mm)



Connectivity to sensor: Packaged B.LV5 Biosensor fits directly (no further cable required); alternatively, general purpose screw terminal connectors are available

Software: Windows-based evaluation software (evaluation license valid for 100 days, contact IST AG for more options)

Product Photo



Order information

Description:	Item number:	Former main reference:
SIX.050.045.100.B.C.B	105453	600.00120

Disclaimer

Not for medical, diagnostics and use on humans. This is an Evaluation Kit solely destined for professionals to be used solely at research and development facilities for such purposes. For more information contact IST AG.



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com