


PLUGGABLE FINISAR[®] TRANSCEIVERS FOR THE DATA CENTER



PLUGGABLE FINISAR® TRANSCEIVERS FOR THE DATA CENTER

The data center ecosystem is going through unprecedented growth and innovation as new players, new business models and new technologies converge. One of the key trends is the growing importance and evolving landscape of fiber optic technologies enabling new architectures and enhanced levels of performance in the data center.

Fiber optics is no longer an optional technology, or only reserved for the toughest interconnect problems. Bandwidth, port density and low-power demands now require fiber optics. And fiber optics is now a pervasive, high-volume, low-cost set of technologies that make it an easy choice for switch interconnect and server I/O.

Coherent is investing heavily in the data center. Our 10G, 25G, 40G and 100G fiber optic products are enabling the highest bandwidth, highest density, lowest power and lowest total cost interconnect solutions on the market today. And we are already working on 200G, 400G and beyond. We are ready to partner with you to push optical interconnect technologies even further to enable unprecedented scale, bandwidth, flexibility and efficiency to the modern, highly-interconnected data center.

Extend Your Data Center Reach

Coherent optical products span all Ethernet data rates currently deployed, from 100Mb/s to 100Gb/s, and we're leading the market with our 25G Ethernet optical transceivers for next-generation servers and switches. Our QSFP products support link distances of up to 500 meters over multimode fiber, well beyond the IEEE Ethernet standard. We also support distances over single mode fiber of up to 20km on 100G QSFP28, 40km on 40G QSFP+ and 80km on 10G SFP+. And if you need to connect your data centers over metropolitan or regional networks, our coherent CFP2-ACO modules can support distances beyond 500km.

Re-Utilize Your Legacy Multimode Fiber Plant

Most data centers today are still architected around 10G Ethernet, focused on 10GBASE-SR links over OM3/OM4 duplex multimode fiber. As data center operators migrate from 10G to 40G and 100G, they want to maintain that existing fiber infrastructure. However, SR4 interfaces require ribbon multimode fiber, and LR4 requires duplex single mode fiber, neither of which are present in the existing duplex multimode fiber plant. Coherent today is supplying QSFP+ and QSFP28 SWDM4 transceivers which provide cost-effective duplex multimode fiber links for both 40G and 100G Ethernet. These duplex multimode transceivers also help decrease fiber infrastructure capex for new data center builds.

Increase Density and Consume Less Power

Coherent understands the importance of heat management in the data center, and has been at the forefront of providing next-generation lower power dissipation optical products.

Our Finisar® 100G QSFP28 optical transceivers (SR4, LR4, CWDM4, and SWDM4) support a maximum power dissipation performance of 3.5 Watts.

Our Finisar® 40G and 100G Quadwire Active Optical Cables provide low-power dissipation settings which the host system can utilize.

We are the market leader in the supply of 12x10G and 12x25G on-board optical Tx/Rx modules, or BOAs. On-board optics enable increased port density while minimizing power dissipation.


Move beyond 100G to 200G / 400G

Coherent has been the market leader in 100G Ethernet modules, supplying CFP modules to service provider router and transport deployments since 2010. We have now expanded our 100G product offering to include various types of CFP2, CFP4, CXP and QSFP28 modules, for telecom and also the emerging data center and enterprise 100G applications.

However, we're not stopping there. We currently have a leading role in standardization activities and are already developing our next-generation Ethernet products, which will support 50G, 200G and 400G data rates in modules like QSFP56, QSFP-DD, and SFP-DD. These products will meet the performance demands of high-performance data centers for many years to come.

PLUGGABLE FINISAR® TRANSCEIVERS FOR THE DATA CENTER

The Modern Highly-Interconnected Data Center



PLUGGABLE FINISAR® TRANSCEIVERS FOR THE DATA CENTER

		Ethernet Data Rates					
Fiber Types	Typical Reach	1G	10G	25G	40G	100G	200G/400G
Active Optical Cables (AOC)	≤100m		SFPwire AOC (FCBG110SD1Cxx)	SFPwire AOC (FCBG125SD1Cxx)	Quadwire AOC (FCBN410QD3Cxx) 4x10G Breakout AOC	Quadwire AOC (FCBN425QE1Cxx) 4x25G Breakout AOC	QSFP-DD 400G Quadwire AOC (FCBx850QE1Cxx)
Duplex Multimode Fiber	≤100m to 180m			SFP28 SR (FTLF8536P4BCL) SFP28 SR Low Latency (FTLF8538P4BCL)	QSFP+ LM4 (FTL4C2QE2C)	QSFP28 SWDM4 (FTLC9152RGPL)	Coming Soon
	≤220m to 500m	SFP SX (FTLF8519P3BNL)	SFP+ SR (FTLX8574D3BCL) SFP+ LRM (FTLX1371D3BCL)	SFP28 eSR (FTLF8540P4BCL)	QSFP+ SWDM4 (FTL4S1QE1C)		
Parallel Multimode Fiber	≤100m			QSFP28 4x25G-SR (FTLC9558REPM) CFP4 4x25G-SR (FTLC9141RENM)	QSFP+ SR4 (FTL410QE4C)	QSFP28 SR4 (FTLC9558REPM) CFP4 SR4 (FTLC9141RENM)	QSFP56 200G SR4 (FTCC8612E1PCM) QSFP-DD 400G SR8 (FTCD8613E1PCM) QSFP-DD 400G SR4.2 (FTCD8633E1PCM)
	≤400m		QSFP+ 4xSR (FTL410QD3C)		QSFP+ eSR4 (FTL410QD4C)		
Duplex Single Mode Fiber	≤500m to 2km		SFP+ LR-Lite (FTLX1374D3BCL)			QSFP28 CWDM4 (FTLC1155RGPL) QSFP28 DR (FTLC4351RHPL) QSFP28 FR (FTLC4351RJPL)	QSFP56 200G FR4 (FTCC1112E1PLL) QSFP-DD 400G FR4 (FTCD4313E1PCL)
	≤10km	SFP LX (FTLF1318P3BTL)	SFP+ LR (FTLX1475D3BCL) SFP+ CWDM (FTLX2471DC0xx)	SFP28 LR (FTLF1436P3BCL)	QSFP+ LR4 (FTL4C1QE2C)	QSFP28 LR4 (FTLC1154RDPL) CFP4 LR4 (FTLC1141RDNL)	QSFP-DD 400G LR8 (FTCD1323E1PCL)
	≤20km to 40km	SFP EX (FTLF1419P1BNL)	SFP+ ER (FTLX1672D3BCL)		QSFP+ ER4 (FTL4E1QE1C)	QSFP28 eLR4 (FTLC1154RDPLA)	
Parallel Single Mode Fiber	≤500m to 2km						QSFP-DD 400G DR4 (FTCD4523E2PCM) QSFP-DD 400G DR4+ (FTCD4533E2PCM)

Please contact Coherent for products supporting other applications and protocols, including Fibre Channel, SONET/SDH/OTN, CPRI/eCPRI, InfiniBand, industrial applications and many others. We have the broadest optical portfolio in the industry.

PLUGGABLE FINISAR® TRANSCEIVERS FOR THE DATA CENTER

Products for the Data Center

Intra-rack

10G & 25G SFPwire®



10G SFP+ SR



25G SFP28 SR
(incl. low latency version)



4x10G QSFP+ SR



4x25G QSFP28 SR
(incl. low latency version)



BOA (optical engine)



4x10G Breakout AOC



4x25 Breakout AOC



Long span/Inter-building

10G SFP+ LR/Bidi/xWDM/Tunable
10/40/80km SMF



25G SFP28 LR
10km SMF



40G QSFP+ LR4/ER4
10/40km SMF



100G QSFP28 CWDM4/LR4/eLR4
2/10/20km SMF



100G CFP4 LR4
10km SMF



100G CFP2 LR4
10km SMF



200G QSFP56 FR4
2km SMF



400G QSFP-DD FR8/LR8
2/10km SMF



CFP2-ACO
Metro/Long Haul
DWDM SMF



Inter-rack

10G SFP+ SR
400m OM4 MMF



10G & 25G SFPwire®
Up to 30m



25G SFP28 SR
400m OM4 MMF



40G QSFP+ SR4/SWDM4
400m OM4 MMF



40G Quadwire®
Up to 100m



100G QSFP28 SR4/SWDM4
100/150m OM4 MMF



100G Quadwire®
Up to 100m



400G QSFP-DD DR4
500m SMF

