



## Features

- 10 kA, 8/20  $\mu$ s surge capability
- Low clamping voltage under surge
- Bidirectional TVS
- Excellent performance over temperature

## Applications

- High power DC bus protection

# PTVS10-xxxC-TH Series High Current TVS Diodes

## General Information

The Model PTVS10-xxxC-TH Series high current bidirectional TVS diodes are designed for use in high power DC bus clamping applications. These devices offer bidirectional port protection and are available with standoff voltage ratings of 58 V and 76 V.

The devices are RoHS\* compliant. They also meet IEC 61000-4-5 8/20  $\mu$ s current surge requirements.



## Absolute Maximum Ratings (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Rating		Symbol	Value	Unit
Repetitive Standoff Voltage	PTVS10-058C-TH PTVS10-076C-TH	$V_{WM}$	58 76	V
Peak Current Rating per 8/20 $\mu$ s IEC 61000-4-5		$I_{PPM}$	10	kA
Operating Junction Temperature Range		$T_J$	-55 to +125	$^\circ\text{C}$
Storage Temperature Range		$T_S$	-55 to +150	$^\circ\text{C}$
Lead Temperature, Soldering (10 s)			260	$^\circ\text{C}$

## Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Parameter	Test Conditions		Min.	Typ.	Max.	Unit
$I_D$ Standby Current	$V_D = V_{WM}$				10	$\mu\text{A}$
$V_{(BR)}$ Breakdown Voltage	$I_{BR} = 10\text{ mA}$	PTVS10-058C-TH PTVS10-076C-TH	64 85	66 92	70 95	V
$V_C$ Clamping Voltage (1) per IEC61000-4-5 (8/20 $\mu$ s current waveform)	$I_{PP} = 10\text{ kA}$	PTVS10-058C-TH PTVS10-076C-TH			110 140	V
$V_{(BR)}$ Temperature Coefficient				0.1		$\%/^\circ\text{C}$
C Capacitance	$F = 10\text{ kHz}$ , $V_d = 1\text{ V}_{rms}$	PTVS10-058C-TH PTVS10-076C-TH		7.5 5.6		nF

(1)  $V_C$  measured at the time which is coincident with the peak surge current.

**BOURNS®**

Asia-Pacific: Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

EMEA: Tel: +36 88 520 390 • Fax: +36 88 520 211

The Americas: Tel: +1-951 781-5500 • Fax: +1-951 781-5700

[www.bourns.com](http://www.bourns.com)

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

# PTVS10-xxxC-TH Series High Current TVS Diodes


**BOURNS®**

## Performance Graphs


### V-I Characteristic



### Percentage $V_{BR}$ Change vs. Junction Temperature



### Typical Surge Current Derating




This graph shows the typical device surge current derating versus ambient temperature when subjected to the 8/20  $\mu$ s current waveform per the IEC 61000-4-5 specification. This device is not intended for continuous operation at temperatures above 125 °C.

# PTVS10-xxxC-TH Series High Current TVS Diodes

**BOURNS®**

## Product Dimensions

Epoxy encapsulation materials conform to UL 94V-0. Silver plated lead finish conforms to the solderability requirements of JESD22-B102, Pb free solder. Package dimensions are shown below:



Dim.	PTVS10-058C-TH	PTVS10-076C-TH
A	$\frac{24.15 \pm 0.72}{(0.951 \pm 0.028)}$	
B	$\frac{2.40 \pm 0.50}{(0.094 \pm 0.020)}$	
C	$\frac{1.75 \pm 1.25}{(0.069 \pm 0.049)}$	
D	$\frac{15.00}{(0.591)} \text{ Max.}$	
E	$\frac{1.25 \pm 0.05}{(0.049 \pm 0.002)}$	
F	$\frac{14.00}{(0.551)} \text{ Max.}$	
G	$\frac{5.00}{(0.197)} \text{ Max.}$	$\frac{6.00}{(0.236)} \text{ Max.}$
H	$\frac{6.00 \pm 1.00}{(0.236 \pm 0.039)}$	

## Typical Part Marking

PTVS10-058C-TH .....10058  
PTVS10-076C-TH .....10076

## How to Order

**PTVS 10 - 076 C - T H**

Series \_\_\_\_\_  
PTVS = Power TVS High Current Diode

Peak Current Rating \_\_\_\_\_  
10 = 10 kA

Repetitive Standoff Voltage \_\_\_\_\_  
058 = 58 V  
076 = 76 V

Suffix \_\_\_\_\_  
C = Bidirectional Device

Package \_\_\_\_\_  
T = Through-Hole

Temperature \_\_\_\_\_  
H = High Temperature Series

REV. 11/15

Specifications are subject to change without notice.  
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.  
Users should verify actual device performance in their specific applications.